



Magflo common spare parts list

Part Number

Sensors:

FDK:085U1052	Terminal box w/lid, 1/2" NPT connections (including internal parts)
FDK:085U1003	Terminal box lid
FDK:085U1005	Sensorprom (programmed), 2K byte
7ME6910-1AA10-1AA0	Mag5000, 115-230 VAC: IP67/NEMA4X
7ME6910-1AA30-1AA0	Mag5000, 11-30 VDC/11-24 VAC: IP67/NEMA4X
7ME6920-1AA10-1AA0	Mag6000, 115-230 VAC: IP67/NEMA4X
7ME6920-1AA30-1AA0	Mag6000, 11-30 VDC/11-24 VAC: IP67/NEMA4X
7ME6920-2CA10-1AA0	Rack-mounted IP20/NEMA2: Mag6000 115-230 VAC
7ME6920-2CA30-1AA0	Rack-mounted IP20/NEMA2: Mag6000 11-30 VDC/11-24 VAC
FDK:085U1039	Display: Mag 5000/6000 (for IP67)
FDK:085U3122	Display: Mag 6000i

Communication modules:

FDK:085U0226	HART
FDK:085U0321	HART – Mag 6000i only
FDK:085U0234	Modbus RTU/RS 485
FDK:085U0236	PROFIBUS PA, Profile 3
FDK:085U0237	PROFIBUS DP, Profile 3
FDK:085U0229	DeviceNet, USMII
A5E02054250	Foundation Fieldbus H1 (Mag 5000/6000 only)

Miscellaneous:

FDK:085U1053	Wall-mount kit for IP67 Mag5000/6000 transmitters, 1/2" NPT
A5E34827189	Remote mounting terminal block kit
A5E02559816	Connection plate/IP67: 115-230 VAC for Mag5000/6000
A5E02559817	Connection plate/IP67: 11-30 VDC/11-24 VAC for Mag5000/6000
A5E02559810	IP20 -19" Rack-mount connection board 11-24 V/115-230 VAC
FDK:085U0220	Submersion kit to be used with remote mounted transmitters
FDK:001STCAB	Standard coil and electrode cable
FDK:001SPCAB	Special electrode cable for empty pipe detection
FDK:085U3123	Mag 6000i electronic module (non-ex)

Siemens Industry, Inc.
Process Industries and Drives
100 Technology Drive
Alpharetta, GA 30005
1-800-365-8766
info.us@siemens.com

Subject to change without
prior notice
Order No.: PIFL-00028-1116
All rights reserved
Printed in USA
© 2016 Siemens Industry, Inc.