

**BMS 151F - Base Unit**

151F-8F PN/DP CPU

<b>AS-HARDWARE - CPU</b>	<b>Siemens MLFB</b>	<b>Qty</b>
SIMATIC DP, IM151-8F PN/DP CPU FOR ET200S, 192 KB WORKING MEMORY, INT. PROFINET INTERFACE (WITH THREE RJ45 PORTS) AS IO-CONTROLLER, W/O BATTERY MMC REQUIRED	6ES7151-8FB01-0AB0	1
SIMATIC S7, MICRO MEMORY CARD P. S7-300/C7/ET 200, 3.3 V NFLASH, 512 KBYTES	6ES7953-8LJ20-0AA0	1

<b>AS-HARDWARE - I/O</b>	<b>Siemens MLFB</b>	<b>Qty</b>
SIMATIC DP, 1 ELECTRON. MODULE FOR ET 200S, 8 DI DC 24V 15 MM WIDTH, 1 PIECE PER PACKAGING UNIT	6ES7131-4BF00-0AA0	2
SIMATIC DP, POWER MODULE PM-E FOR ET 200S; 24V-48V DC WITH DIAGNOSIS	6ES7138-4CA50-0AB0	1
SIMATIC DP, ELECTRON. MODULE F. ET200S, 4/8 F-DI PROFISAFE, 24V DC, 30 MM WIDTH UP TO CATEGORY 4 (EN954-1)/ SIL3 (62061) ALSO USEABLE IN PROFINET- NETWORK WITH IM151-3 HF	6ES7138-4FA04-0AB0	2
SIMATIC DP, ELECTRON. MODULE F. ET200S, 4 F-DO PROFISAFE, DC 24V/2A, 30 MM WIDTH UP TO CATEGORY 4 (EN954-1) ALSO USEABLE IN PROFINET- NETWORKS WITH IM151-3 HF	6ES7138-4FB03-0AB0	2
SIMATIC DP, 5 UNIVERSAL TERMINAL MODULES TM-E15S26-A1 FOR ET 200S FOR ELECTRONIC MODULES 15MM WIDE, SCREW-TYPE TERMINALS 2X6 TERMINAL CONNECTIONS WITH TERMINAL LEAD TO AUX1, AUX1 IN LINE, 5 PIECES PER PACKAGING UNIT	6ES7193-4CA40-0AA0	1
SIMATIC DP, TERMINAL MODULE TM-P15S23-A0 FOR ET 200S FOR POWER MODULES 15 MM WIDE, SCREW-TYPE TERMINALS 2X3 TERMINAL CONNECTIONS WITH TERMINAL LEAD TO AUX1 AUX1 INTERRUPTED	6ES7193-4CD20-0AA0	1
SIMATIC DP, TERMINAL MODULE TM-E30S46-A1 FOR ET 200S FOR ELECTRONIC MODULES 30MM WIDE, SCREW-TYPE TERMINALS 4X6 TERMINAL CONNECTIONS WITH TERMINAL LEAD TO AUX1, AUX1 IN LINE,	6ES7193-4CF40-0AA0	6
SIMATIC DP, 5 ELECTRON. MODULES FOR ET 200S, 4 DO STANDARD DC 24V/0.5A, 15 MM WIDTH, 5 PIECES PER PACKAGING UNIT	6ES7132-4BD02-0AA0	1

<b>AS-HARDWARE - HMI</b>	<b>Siemens MLFB</b>	<b>Qty</b>
SIMATIC MP 277 10" TOUCH	6AV6643-0CD01-1AX1	1