



SIEMENS

Ingenuity for life

19" Ethernet layer 2 switches

RUGGEDCOM Datasheet

Rack-mounted Ethernet Layer 2 switches deliver utility-grade performance, reliability and field-proven MTBF to lower OPEX costs.

Designed to operate reliably in harsh environments, the RSG2000 product family provides a high level of immunity to electromagnetic interference and heavy electrical surges typical of environments found in utility substations, rail applications, and oil and gas operations. An operating temperature range of -40°C to +85°C coupled with hazardous location compliance (Class 1 Division 2), optional conformal coating and a galvanized 1U form factor steel enclosure with industrial grade DIN, panel, or 19" rack-mounting options allows the RSG2000 family of switches to be placed in almost any location.

The embedded Rugged Operating System (ROS) provides advanced cyber security features and comprehensive networking functions such as Enhanced Rapid Spanning Tree (eRSTP), Port Rate Limiting, and a full array of intelligent functionality for high network availability and manageability. Coupled with ruggedness and durability that is

designed in from the onset, the RSG2000 product family is ideal for creating mission critical, real-time, control applications where high reliability and availability is of paramount importance.

All RUGGEDCOM products are backed by a five year warranty and unsurpassed technical support.

Common features

- Large variety of fiber ports available
- High immunity to EMI and heavy electrical surges
- Low voltage DC input and high voltage AC/DC input options

- -40°C to +85°C operating temperature (no fans)
- Fully integrated power supply (no external adaptors)
- Long haul fiber support

[RUGGEDCOM Product Information](#)

[General background information](#)

[RUGGEDCOM Brochures and information material](#)

Product Family Overview

[Family brochure](#)

[Ordering overview](#)

[RUGGEDCOM RST2228 Technical Brochure](#)



The tool for selection and configuration of RUGGEDCOM products.

[RUGGEDCOM Selector](#)

Unrestricted

RUGGEDCOM RSG2100 / RSG2100P

19-port modular managed Ethernet switch with Gigabit uplinks

- 3 x 1000BASE-X + 16 x 10/100BASE-X
- Hazardous location certification: Class 1 Division 2
- Power-over-Ethernet (PoE) version available

Data Sheet:

[RSG2100](#)

[RSG2100P](#)

User Guide:

[RSG2100/RSG2100P](#)

Installation Guide:

[RSG2100](#)

[RSG2100P](#)



RUGGEDCOM RSG2200

9-port managed Gigabit Ethernet switch

- 1000BASE-X and/or 10/100/1000BASE-T
- Hazardous location certification: Class 1 Division 2

Data Sheet:

[RSG2200](#)

User Guide:

[RSG2200](#)

Installation Guide:

[RSG2200](#)



RUGGEDCOM RSG2288

9-port managed Gigabit Ethernet switch with IEEE 1588 v2 and IRIG-B conversion

- 1000BASE-X and/or 10/100/1000BASE-T
- Available PTP module provides GPS time source and IRIG-B in/out

Data Sheet:

[RSG 2288](#)

User Guide:

[RSG 2288](#)

Installation Guide:

[RSG 2288](#)



RUGGEDCOM RSG2300 / RSG2300P

32-port managed Ethernet switch with Gigabit uplinks

- 24 x 10/100BASE-TX + 8 x 10/100BASE-X or 4 x 100/1000BASE-X and 4 x 10/100BASE-X
- Hazardous location certification: Class 1 Division 2
- Power-over-Ethernet (PoE) version available

Data Sheet:

[RSG2300](#)

[RSG2300P](#)

User Guide:

[RSG2300/2300P](#)

Installation Guide:

[RSG2300](#)

[RSG2300P](#)



RUGGEDCOM RSG2488

28-port advanced utility-grade, high density managed Gigabit Ethernet switch

- Field replaceable Ethernet and time synchronization media modules
- Hot-swappable power supplies
- 28 x 1000BASE-X non-blocking architecture
- PTPv2 hardware time stamping

Data Sheet:

[RSG2488](#)

User Guide:

[RSG2488](#)

Installation Guide:

[RSG2488](#)



RUGGEDCOM RST2228 New

28-port advanced utility-grade, managed field modular IEEE 1588 switch with 10 Gbit/s uplinks

- 4 x 100BASE-X/10GBASE-X uplinks
- Up to 24 x 10/100/1000BASE-X ports
- Field-modular 4-port modules for added flexibility
- IEEE 1588 v2 with hardware time stamping

Data Sheet:


[RST2228](#)

User Guide:

[RST2228](#)

Installation Guide:

[RST2228](#)



Published by
Siemens Industry, Inc. 2018.

Siemens Industry, Inc.
5300 Triangle Parkway
Norcross, GA 30092

For more information, please contact
our Customer Support Center.
Phone: 1-800-241-4453
E-mail: info.us@siemens.com

usa.siemens.com/ruggedcom

©2018 Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.

Unrestricted