




Lighting Contactor
Class LE
Electrically Held
20 Amp, 4 Pole

August 2012

General technical data:	
Finger-safe (main circuit / control circuit)	yes / yes
Degree of pollution	3
Altitude (m)	2,000
Ambient storage temperature (°C)	-55 to 80
Ambient operating temperature (°C)	0 to 40
Humidity (% non-condensing)	10 to 95
Shock resistance at rectangular impulse (g/ms)	6.7 / 5, 4.2 / 10
Shock resistance at sine pulse (g/ms)	10.5 / 5, 6.6 / 10
Rated impulse voltage resistance (kV)	no data
Rated insulation voltage (V)	no data
Mechanical operating cycles as operating time:	
of contactor	30,000,000
of contactor with additional aux contacts	10,000,000
Main circuit:	
Number of NC / NO main contacts	0NC / 4NO
Typical power loss per conductor (W)	0.7
Off-load operating frequency (cycles per hour)	10,000
Current ratings:	
Tungsten (poles per phase)	20A @277V 1p 1ph
	20A @480V 2p 1ph
	20A @480V 3p 3ph
Ballast (poles per phase)	20A @347V 1p 1ph
	20A @600V 2p 1ph
	20A @600V 3p 3ph
General & resistive (poles per phase)	20A @600V 1p 1ph
	20A @600V 2p 1ph
	20A @600V 3p 3ph
Coil ratings:	
Inrush / sealed power (VA)	31.7 / 4.8
Coil voltage tolerance factor	0.8 - 1.1
Coil code 024	24VAC 60HZ
Coil code 120	110VAC 50HZ / 120VAC 60HZ
Coil code 208	198VAC 50HZ / 208VAC 60HZ
Coil code 240	220VAC 50HZ / 240VAC 60HZ
Coil code 277	277VAC 60HZ
Coil code 347	347VAC 60HZ
Coil code 480	480VAC 60HZ
Coil code 600	600VAC 60HZ
Internal/standard auxiliary contact:	
Number of NC / NO auxiliary contacts	(must use an external/optional auxiliary contact)
Rating	NA

Installation/mounting/dimensions:	
Mounting orientation	vertical
Type of mounting: screw / DIN rail	yes / yes
Height x Width x Depth (mm)	57.5 x 45 x 73
Minimum clearance to sides (mm)	0
Minimum clearance to earthed parts (mm)	6
Connection type / torque for main circuit terminals	screw / 7-10 lb in
Connection type / torque for control circuit terminals	screw / 7-10 lb in
Solid & stranded conductors for main contacts (AWG)	2x(20-16), 2x(18-14), 2x(12)
Solid & stranded conductors for control circuit (AWG)	2x(20-16), 2x(18-14)
Conductor type for main and control circuits	75°C CU
Short circuit current rating of main circuit:	
Short circuit current rating	5kA @ 600V
Max fuse / circuit breaker (Amp)	30 / 25
Certificates:	
	cULus

Dimensions



Wiring Diagram

