

SIEMENS

Ingenuity for life

Pointek CLS200

Precise and versatile

usa.siemens.com/level

Inverse frequency shift capacitance level switch

Pointek CLS200 is a versatile inverse frequency shift capacitance level switch ideal for level detection of liquids, solids, slurries, foam, pump control and interfaces in general process conditions with high chemical and physical abuse. It includes Advanced Sensitive-Tip technology, ensuring high accuracy, resolution and repeatability. The digital version (with PROFIBUS PA) includes a display and provides additional diagnostic features.

- Inverse frequency shift capacitance technology results in higher accuracy and resolution
- Unique potted construction protects signal circuit board from shock, vibration, humidity, and/or condensation
- Insensitive to product buildup due to high frequency oscillation
- Level detection independent of tank or pipe earth ground reference
- Integral LCD display allows for easy setup of CLS200 when you can configure switching threshold, even under the most demanding process conditions
- Standard version: 3 LED indicators for adjustment control, output status and power
- Advanced Sensitive-Tip technology for accurate and repeatable switch point in a wide range of liquids, solids, or slurry applications
- Online commissioning of parameters allows full advantage of the instrument: number of counts, setpoints, adjustable hysteresis, time delay, and output status. You can set up and make adjustments from the control room or other remote locations
- SIL-2 qualified for overspill protection in accordance with IEC 61508





Pointek CLS200	Standard	Digital
----------------	----------	---------

Power	12 to 250 V AC/DC, 0 to 60 Hz max. 2 W	<ul style="list-style-type: none"> Standard: 12 to 30 V DC, 12.5 mA Intrinsically safe: 12 to 24 V DC, 12.5 mA
--------------	--	--

Interface		
Configuration	Locally using dip switches and potentiometers	<ul style="list-style-type: none"> Remotely using SIMATIC PDM Locally using 3 button keypad
Display	Transmitter with 3 LED indicators	Local digital LCD display
Communication		<ul style="list-style-type: none"> PROFIBUS PA (IEC 61158 CPF3 CP3/2) Bus physical layer: IEC 61158-2 MBP-(IS) Device profile: PROFIBUS PA profile for Process Control Devices Version 3.0, Class B FISCO field device
Output	<ul style="list-style-type: none"> Relay: 1 SPDT Form C relay Time delay: (on and/or off) controlled by user Solid state switch Fail-safe mode 	<ul style="list-style-type: none"> Solid-state switch Time delay: (on and/or off) controlled by user Fail-safe mode

Mechanical		
Enclosure	<ul style="list-style-type: none"> Epoxy coated aluminum with gasket IP65/Type 4 /NEMA 4 (optional IP68) Installation category: II Pollution degree: 4 	
Process connection	<ul style="list-style-type: none"> 316 stainless steel (1.4404) (standard and cable) Thermal Isolator 	
Sensor	<ul style="list-style-type: none"> Sensor PPS (optional: PVDF) Max. 5.5 m (18 ft); extension 316 stainless steel (1.4404) (Standard and Sanitary) Max. 30 m (98.4 ft) liquids and slurries; 5 m (16.4) solids (under loads); extension (stainless steel) with FEP coating (Cable) 	

Process conditions		
Ambient temperature	-40 to 85 °C (-40 to 185 °F)	
Process temperature standard	<ul style="list-style-type: none"> Standard -40 to 85 °C (-40 to 185 °F) With temperature extension: -40 to 125 °C (-40 to 257 °F) 	
Pressure	<ul style="list-style-type: none"> Standard and rigid extension versions -1 to 25 bar g/365 psi g (nominal) Cable version -1 to 10 bar g/150 psi g (nominal) Optimal slide coupling version: -1 to 10 bar g/150 psi g (nominal) 	
Dielectric constant ϵ_r	Min. 1.5	

Approvals	CE, CSA, FM, ATEX, SIL-2, C-TICK, WHG Overfill Protection (Germany), Lloyd's Register of Shipping, categories ENV1, ENV2, and ENV5, Pattern Approval (China)
------------------	--

Pointek is a registered trademark of Siemens Milltronics Process Instruments Inc.
 * Pressure is temperature dependent. SIMATIC PDM is a registered trademark of Siemens.
 © 2016 Siemens Milltronics Process Instruments Inc.

Siemens Industry, Inc.
 100 Technology Drive
 Alpharetta, GA 30005
 1-800-365-8766
 info.us@siemens.com

Subject to change without prior notice.
 Order No.: PIFL-5KK03-1016
 All rights reserved
 Printed in the USA
 © 2016 Siemens Industry, Inc.

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.