



SIEMENS



Controls Express Program

A large selection of NEMA enclosed starters and pump panels now offered with faster shipping as a standard



Accelerated shipments to your door

Siemens NEMA starters and enclosed starters are known for their dependability and ruggedness; and now they are delivered even faster than before. 5 to 10 day lead time turns into a 1 to 2 day lead time.

Some of our most popular Class 14 starters and Class 87 pump panels will be available for routine expedited delivery directly from the stocked supply in our West Chicago facility. The shipping process will start immediately once an order is received, resulting in a very fast turnaround time.

We understand the needs of our customers so we have selected over 2200 of our most popular SKUs ordered to be a part of this new and exciting program. We will stock all of the components for these enclosed starters at our West Chicago facility and have our production lines ready to build once an order is received.



Reliability Built In

Siemens starters in NEMA enclosures are capable of withstanding the most severe and demanding industrial, continuous-duty applications. Siemens offers a complete and diverse range of NEMA enclosed starters that includes motor-matched half sizes in addition to standard full NEMA sizes. Siemens starters offer unsurpassed protection and performance. Along with quick ship program, our products can now get to our customers more efficiently than ever.

usa.siemens.com/controls



Ready When You Are

The following Class 14 starters and Class 87 pump panels are now available in stock for same day or next day shipping (based on time of day when order is received) to customers in North America. Eligibility for the program from the main distribution center in West Chicago extends to orders with a threshold of 6 for the Class 14 and a threshold of 6 for the Class 87. Please contact customer service at 1-800-241-4453 for additional order volumes.

Faster Delivery on over 2,200 Enclosed Starter

In January 2012, we began our new Controls Express program. In this program, we have picked 2,200 of the most popular Siemens enclosed NEMA starter styles that includes class 14s, 17s, 18s, 40s, 87s, and CLMs. The new lead times for each one of these items will now be 1 to 2 days.

All enclosed starters, pump panels and lighting panels ordered through the in stock / controls express program are returnable under the standard Siemens return policy.

Class 14 Starters with NEMA 1 Enclosures*	
14BUB32BA	14DUD32BA
14CP32BA81	14DUD32BC
14CUB32BA	14DUE32BC
14CUC32BA	14DUE32BA
14CUC32BF	14EUE32BA
14CUD32BA	14FUF32BA
14DUC32BA	14FUF32BC

Class 87 Pump Panel with NEMA 3R Enclosures*	
87DUC6FC	87GUG6FC
87DUD6FA	87HUG6FA
87DUD6FC	87HUG6FC
87DUE6LC	87HUG6MC
87EUE6FC	87IUH6FC
87FUF6FA	87JUH6FA
87FUF6FC	87JUH6FC
87FUF6MC	

*All enclosed starters, pump panels and lighting panels ordered through the in stock / quick ship program are returnable under the standard Siemens return policy.



Siemens Industry, Inc.
Industry Automation
3333 Old Milton Parkway
Alpharetta, GA 30005

info.us@siemens.com

1-800-214-4453

Subject to changes without prior notice
Printed in USA
Order No: NEFL-ENCST-1111

©2012 Siemens Industry, Inc.

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract. All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.