

Klingelberg-Oerlikon Technical Center

HELPS DANA CUT CYCLE TIME

Approximately one year ago, Dana Corp.'s facility in Glasgow, KY, found itself—in the words of one of its manufacturing engineers—“in a very severe situation.”

Specifically, part demand was such that the facility was not able to achieve desired capacity levels, says Lance Dement, manufacturing engineer and Six Sigma black belt at Dana.

One production gear used in a Class 8 truck axle was an 8822 steel part approximately 18” in diameter and weighing 100 lbs. before tooth cutting. In order to meet the capacity requirement, operators needed to remove 17 lbs. of steel and reduce the cycle time to less than 12 minutes.

The solution, as it turns out, was the right combination of machine and CNC control: the Klingelberg C60 equipped with a Siemens Sinumerik 840D CNC.

Produced on a C60 at Dana's site in Glasgow (KY), this gear was used in a Class 8 truck axle.



Klingelberg of Germany, recognized as specialists in servicing gear machinery for automotive, truck, bus and off-road heavy axle manufacturers, wanted to provide the market with a more universal machine with an easier-to-use programming interface, fitted with a controller that provided optimum drive accuracy and maximum diagnostic capability. And the cheaper this could be done, the better.

After weighing several alternatives, the engineers at Klingelberg settled on the Siemens Sinumerik 840D CNC to provide onboard control of linear and rotational axis movement.

Klingelberg chose Siemens controls to work with its C27, C42 and C60 spiral bevel gear cutting machines because of the control's self-diagnostic and intuitive troubleshooting capabilities. “The user interface is very powerful, especially when locating the root cause of a machine problem,” says Frank Irey, vice president and general manager of Klingelberg's U.S.-based service division, Klingelberg Oerlikon Technical Center (KOTC).

The Klingelberg C60 and the Siemens CNC were a natural fit, according to Irey. Klingelberg had previously utilized the Sinumerik 840D CNCs for its line of G30/G60 bevel gear grinders and B27 blade grinders.

All of these innovations did not mean totally smooth sailing for the manufacturing operation. Dement says that initially the cutter damage was serious, and the team had to work around it by reducing the transit time while maintaining cutter life.

Klingelberg devised a program with the Siemens Simatic Step 7 software to enable Dana's operators and production engineers to monitor and adjust the cycles for overall process improvement. These adjustments were easily made by Dana's operators to quickly maintain quality. The cycle time was cut in half.

KOTC is continuing to work with Dana to enable the company to store gear programs on a network. “The cutting machines are networked to the Klingelberg P Series inspection machines and are

Portable CNC gear pitch tester ES 4100





The new portable pitch measuring instrument ES 4100 offers an extremely exact method of measurement. A high degree of operational convenience is possible by the built in processing of the measured data and the tilt and Swivel display touch-screen. ISO, DIN or AGMA standards evaluation software. The measurements can be stored and printed out on an external PC. Existing pitch measuring instrument ES401 from the former MAAG company can also be updated on request.

Representative USA:
GEAR METROLOGY, Inc.
 Tel: 686-686-5746
 gearmet@frontiernet.net

Donner + Pfister AG
 Switzerland Tel: +41554402032
 www.dpag.ch info@dpag.ch

Application engineers maintain the Klingenberg C60 gear generating machines.



being equipped with our KOMET gear cutting corrections software package, so machine corrections can be directly transferred from the inspection machine to the cutting machine controller," says Irey. "This is primarily to eliminate 'fat finger' data entry error."


Every C Series machine comes with a LAN card in the controller that accommodates LAN connections. The connections are then used to store and retrieve program data off-line within the company. Also standard to this series is a modem that can be connected to a standard telephone line. So, a dial-up connection can be made that facilitates on-line, real-time service diagnostics from the KOTC facility in Saline. The service also supports software upgrades, and customers can download them remotely. According to Irey, most of KOTC's customers use both features.

"KOTC offers the best possible support for their machine tool operations. We often talked in the middle of the night about various service issues," says Dement. "They definitely have an edge." ■

The Klingenberg C60 spiral bevel generating machine w/Siemens SINUMERIK 840 D CNC on board.




DIANAMIC



**STANDS FOR
 SERVICE, RELIABILITY and QUALITY**

Since 1985, Dianamic Abrasive Products, Inc. has manufactured and distributed Diamond and CBN grinding wheels and tooling.

Dianamic is the exclusive aftermarket distributor for Reishauer Diamond dressing tools, which can be used on all types of gear grinding machines from various manufacturers, including Reishauer, Kapp, Gleason, Koepfer, Maag, Mitsubishi, Pfauter, Fassler, Star SU, Samputensili, Bourn & Koch, Nachi and Liebherr.



DIANAMIC® Abrasive Products Inc.
 2566 Industrial Row • Troy, Michigan 48064, USA

Telephone: (248) 280-1185 Fax: (248) 280-2733
 Website: www.dianamic.com E-mail: info@dianamic.com