

# SIEMENS

*Ingenuity for life*



Analytical Products and Solutions

## ULTRAMAT 23 Gas Analyzer

Continuous and economical gas measurement

[usa.siemens.com/cga](http://usa.siemens.com/cga)

The well proven ULTRAMAT 23 gas analyzer provides a perfect and economical yet powerful continuous gas measurement. With single or dual NDIR channels up to three infrared absorbent gas components can be measured simultaneously. By means of an additional sensor Oxygen or H<sub>2</sub>S can be added. The multi-layer IR detectors permit highly selective measurement and therefore minimizes cross interference. It is available in a 19" rack or desk top design with an internal or external pump. Results and status information are communicated via serial or analog means.

The compact well proven design combines the measurement of infrared active gases with O<sub>2</sub> or H<sub>2</sub>S in a single unit. Utilizing ambient air for validation, simplifies the system solution and reduces operational cost without sacrificing performance. Proven design ensures simple maintainability. The versatility permits selection of the best combination of key components in a single unit for continuous analysis of a wide variety of measurements from combustion emission, biogas, heat treating to cement production and many others.

The ULTRMAT 23 is used for the measurement of a wide variety of components that absorb in the infrared spectrum. The multicomponent NDIR technology design permits the measurement of up to three constituents simultaneously in an economical and space saving manner. The sample gas does not come in contact with the measurement sensor and therefore cannot be contaminated. The robust and corrosive resistant measuring cell can easily be cleaned in case of fouling. The measurement of Oxygen is achieved with an electrochemical cell or for lower concentrations and wet gases, it is measured with a paramagnetic dumbbell cell. Hydrogen Sulfide is measured with an electrochemical cell. The comprehensive design includes the flow control, optionally a pump as well as relays for status indication and external stream switching. The integrated automatic calibration function utilizing ambient air enables maximum ease of use and minimum maintenance attention for effective economic and reliable operation.

## Applications

Because the versatility ULTRMAT 23 is widely utilized:

- Biogas from digester, fermenters and landfills
- Rotary kiln effluent in cement industry
- Metal heat treating atmosphere control
- Combustion engine emission testing
- Vent emission monitoring
- Atmospheric control in green houses, during fruit transportation and warehouse storage
- Furnace effluent monitoring
- Medical gas monitoring

## Technical Details

Number of components	up to 3 IR + O <sub>2</sub> or H <sub>2</sub> S
Measuring components	CO, CO <sub>2</sub> , CH <sub>4</sub> , C <sub>2</sub> H <sub>4</sub> , NO, SO <sub>2</sub> , SF <sub>6</sub> , O <sub>2</sub> , H <sub>2</sub> S
IR Smallest measuring range	Component specific: 0-50 vpm / 0-500 vpm
O <sub>2</sub> measuring range	0-5% / 0-25% EC and 0-2% / 0-100% Dumbbell
H <sub>2</sub> S measuring range	0-5 / 0-50 vpm
Auto Calibration	Ambient air for IR components
Housing	19" Rack Mount or Desktop (Portable)
Communication	Analog Outputs, RS485, Profibus PA/DP, SIProm GA

### For more information, please contact:

Siemens Industry, Inc.  
 5980 West Sam Houston Parkway North  
 Suite 500  
 Houston, TX 77041  
 Phone: 713-939-7400  
 Email: ProcessAnalyticsSales.industry@siemens.com

## Your Benefits

- **Economic operation**
  - Multicomponent measurement often permits utilizing a single analyzer unit.
  - Validation with ambient air minimizes analyzer test gas consumption.
  - Very beneficial cost performance ratio.
- **Reliability**
  - Multi-layer detector, inert absorption cell, flow control and auto calibration promotes long term stability and minimizes cross interference.
  - Service information and logbook assists in recognizing or diagnosing maintenance.
- **Communication**
  - Simplified operating interface and remote operation and control via open interface architecture.
- **Product quality**
  - IR sensor not wetted.
  - Inert and cleanable measuring cell.
- **Measurement system solution**
  - Single source responsibility
  - Front end engineering assistance for proper system solution.
  - Best product, sample and measurement system solution
  - Installation and commissioning
  - Life time support responsibility

Siemens Flyer  
 June 2018

Published by  
 Siemens Industry, Inc.

Process Automation  
 Process Industries and Drives  
 100 Technology Drive  
 Alpharetta, GA 30005

1-800-964-4114  
 info.us@siemens.com

Subject to change without prior notice  
 Order No.: PIAFL-00071-0618  
 Printed in USA  
 All rights reserved  
 © 2018 Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.