

SIEMENS



Process Instrumentation

The best just got better.

Meet the enhanced MultiRanger 200 – easier to use, easier to set up. Just plain better.

For close to thirty years, the MultiRanger 200 has been the industry standard for level measurement in water/wastewater monitoring and pumping, inventory management, truck load-outs, open channel monitoring, and anything in between.

Now we've made the best even better.

The enhanced MultiRanger 200 gives you unparalleled ease of use, setup in under a minute, customer-driven features, and PROFIBUS DPV1. All to make your work simpler and to provide the reliability you have grown to trust in Siemens ultrasonic controllers.

Welcome to the enhanced MultiRanger 200 – easier to use, easier to set up. In short? Just plain better.



usa.siemens.com/level

Meet the best of the best

Since the early 1970s, Siemens has been your partner in ultrasonic level measurement. This experience matters. The MultiRanger 200 ultrasonic level controller has been a star for decades – now it's time to meet the better, easier-to-use, enhanced MultiRanger 200.

All of your favorite features in one newly enhanced package. You want it, we've got it:

Easy setup

- Programmable in under a minute with an improved Human Machine Interface (HMI) and Quick Start Wizards.
- Redesigned enclosure with a protected wiring compartment, removable terminal blocks, and an updated exterior.

Advanced software

- As always, we deliver Sonic Intelligence, our patented echo processing technology for ultrasonic level measurement.
- Advanced algorithms provide intelligent processing of echo profiles. The result? Repeatable, fast, and consistent measurement you can trust.

Compatibility and connectivity

- A range of communications options including PROFIBUS DPV1.

- Compatible with Siemens Echomax ultrasonic non-contacting transducers – impervious to dust, moisture, vibrations, flooding, and high temperatures.

- Siemens transducers have active faces to reduce material buildup and maintenance – an ideal fit for a wide range of industries. Pair with a submergence shield for the ability to sense flooding or overflow conditions.

Cost savings and improved safety

- Install the new MultiRanger 200 and operations are immediately more cost-effective: inventory monitoring is always precise, processes can be easily controlled, and expensive spill cleanups can be avoided.
- A reliable ultrasonic level controller reduces the need to send operators to the application for maintenance. Keep workers out of hazardous situations and you reduce the chance of accidents and the consequences to your company.

Want the best of the best? Simply unplug your existing MultiRanger 200 and plug in the enhanced MultiRanger 200 – same wiring connections, same mounting, same size. Easy enough, right?

What's enhanced

- **Improved HMI for unparalleled ease of use** – local four-button programming and menu-driven parameters.
- **Setup in under a minute** – faster commissioning with graphical Quick Start Wizards.
- **Re-designed enclosure** – fully isolated electronics, removable terminal blocks, and an updated exterior.
- **Improved PROFIBUS DPV1 connectivity** – increased interaction with this popular industrial communication protocol.





MultiRanger 200	
Order No.	7ML5034
	MultiRanger 200 is a versatile non-contacting ultrasonic level controller for up to six pumps and provides control, differential control, and open channel flow monitoring for short- to medium range applications in virtually any application in a wide range of industries.
Range	0.3 to 15 m (1 to 50 ft), transducer and material dependent
Accuracy	6 mm (0.24") or 0.25% of maximum range (whichever is greater)
Key features	<ul style="list-style-type: none"> • Monitors water and wastewater of any consistency up to 15 m (50 ft) in depth • Single-point monitoring with all models, optional dual-point monitoring and gate control • Simple setup with graphical Quick Start Wizards on the local user interface with four-button programming • Supports remote configuration and diagnostics with SIMATIC PDM and optional PROFIBUS DPV1 • Auto False-Echo Suppression to avoid false echoes from fixed obstructions • Digital communications with built-in Modbus RTU via RS-485 • Digital input for back-up level override from point level devices • Accurate and repeatable open channel flow measurements
Applications	<ul style="list-style-type: none"> • Level measurement or pump control in water/wastewater • Truck load-outs • Inventory management in industrial storage vessels • Open channel monitoring
Communications or outputs	<ul style="list-style-type: none"> • RS-485 with Modbus RTU or ASCII • Compatible with SIMATIC PDM via Modbus RTU <p>Options</p> <p>SmartLinx cards for PROFIBUS DPV1, DeviceNet</p>
Approvals	CE, CSA ^{NRULC} , UL, FM, RCM

Ultrasonic advantage

- Easy to use and quick to configure – Graphical Quick Start Wizards guide you during setup.
- Auto False-Echo Suppression – differentiates false echoes from true material level echoes.
- Sonic Intelligence – our field-proven echo processing algorithms provide the most reliable performance possible.
- Compatibility with Siemens Echomax transducers




Find out more:

www.usa.siemens.com/pi

Find out more information about how the MultiRanger 200 can cost-effectively solve your application needs.

Let us show you what better is.



Subject to change without prior notice
Order No.: PIBR-00016-0815
All rights reserved
Printed in USA
© 2015 Siemens Industry, Inc.

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.

More information:
info.us@siemens.com

Follow us on:
www.facebook.com/siemensii
<https://twitter.com/siemensii>
www.youtube.com/siemens
<https://blogs.siemens.com/measuringsuccess>

Siemens Industry, Inc.
3333 Old Milton Parkways
Alpharetta, GA 30005
1-800-241-4453