

SIEMENS

Ingenuity for life



Process Instrumentation

The world's most accurate level controller

SITRANS LUT400: precision built on decades of experience.



usa.siemens.com/level

The world's most accurate ultrasonic controller for level measurement

Customer-driven features. Setup in under a minute. Intuitive operation.

All of this plus a world-leading accuracy of 1 mm (0.04").

Siemens brings you the SITRANS LUT400 series ultrasonic controllers. Compact, single point controllers that excel at continuous level monitoring and control in liquid, solid, or slurry applications in a wide range of industries.

Three models make up the series:

- SITRANS LUT420 Level and Volume Controller
- SITRANS LUT430 Level, Pump, and Flow Controller
- SITRANS LUT440 High Accuracy Open Channel Monitor (OCM), which also provides a full suite of advanced level, volume, and pump controls

These controllers are flexible solutions for a world of applications: water/wastewater monitoring and pumping, inventory management, crusher control, truck load-outs, or anything in between.

High accuracy keeps operations in all of these applications cost-effective: inventory monitoring is always precise, processes can be better controlled, and expensive spill cleanups can be avoided.

A reliable ultrasonic level controller reduces the need to send operators to the application for maintenance. By keeping workers out of hazardous situations altogether, you can immediately reduce the chance of accidents and the consequences to your company.

SITRANS LUT400 series features Siemens' patented Sonic Intelligence, which continuously evaluates and adjusts for noise level and changing process conditions. The controllers have three relays combined with a suite of pump, alarm, and other control features.

All three models are compatible with the full line of Siemens Echomax transducers. These transducers feature self-cleaning faces and submergence detection, and are impervious to dust, moisture, vibrations, and flooding, making them an ideal fit for a wide range of industries.



Installing SITRANS LUT400 series controllers is simple with a selection of mounting options, whether you prefer a DIN rail, pipe, or wall mount. Operators can program the controllers in less than a minute using the four-button local user interface and intuitive menu options.

- **Industry-leading accuracy** – SITRANS LUT400's ± 1 mm (0.04") accuracy gives you confidence in your measurements
- **Easy to use** – local user interface with four-button programming, menu-driven parameters, and Wizard support for key applications
- **Quick to configure** – graphical Quick Start Wizards guide you during setup
- **Next generation Sonic Intelligence** – improved performance in noisy environments thanks to digital receiver technology
- **Consistently high performance** – patented digital receiver technology ensures reliability even in the harshest environments
- **Saving you money** – energy-saving algorithms and real-time clock help you reduce pump operation costs by avoiding peak energy periods
- **Integrated datalogger** – record historic performance and alarm events
- **Communications convenience** – HART® communications with access via the local user interface, SIMATIC PDM, Emerson AMS™, Field Device Tool (FDT), Field Communicator 375/475 (FC375/FC475), and web browser
- **Enhanced diagnostics** – echo profile and trend view on the display
- **Installation simplicity** – wall, pipe, and DIN rail mounting configurations with ¼-turn fasteners for quick access and hassle-free wiring with removable terminal strips

Standard specifications	SITRANS LUT400 series
Range	0.3 to 60 m (1 to 200 ft), transducer and material dependent
Accuracy	<ul style="list-style-type: none"> • Standard accuracy: ± 1 mm (0.04") plus 0.17% of distance* • High accuracy configuration (SITRANS LUT440): ± 1 mm (0.04"), within 3 m (10 ft) range
Resolution	0.1% of measured range or 2 mm (0.08"), whichever is greater
Ambient temperature	-20 to 50 °C (-4 to 122 °F)
Application temperature	-40 to 150 °C (-40 to 302 °F)
Interface	<ul style="list-style-type: none"> • Back-lit LCD 60 x 40 mm (2.36 x 1.57") • Removable display, operational up to 5 m (16 ft) from enclosure base
Communications	HART, USB
Programming	Four local push buttons, SIMATIC PDM, Emerson AMS, web browser (Internet Explorer), FDT, FC375/475
Output	<ul style="list-style-type: none"> • Three relays: one form C (SPDT) relay, two form A (SPST) relays • One 4 to 20 mA output (active or passive)
Input	<ul style="list-style-type: none"> • Two discrete inputs (0 to 50 V DC max switching level) with 24 V DC bias for contact level device and/or pump interlock • One temperature sensor input for optional TS-3 temperature sensor
Enclosure	Wall/Pipe/DIN rail mount <ul style="list-style-type: none"> • ½ DIN - (HxWxD): 144x144x146 mm (5.7x5.7x5.75") • Type 4X/NEMA 4X/IP 65***, panel mount display IP 54 (Type 3/NEMA 3/IP 54) • Polycarbonate
Power	<ul style="list-style-type: none"> • AC version: 100 to 230 V AC $\pm 15\%$, 50/60 Hz, 36 VA 10 W • DC version: 10 to 32 V DC 10 W
Approvals	<ul style="list-style-type: none"> • General purpose: CE, CSA_{USIC}, FM, UL Listed, C-TICK • Hazardous location: Canada - CSA Class I, II, III, Division 2 (Groups A, B, C, D, F, G)

* Standard accuracy: ± 1 mm (0.04") plus 0.17% of distance applies to all models excluding SITRANS LUT440 in high accuracy mode.

** Note: use of the knock-out on the blind lid for the panel mount version reduces the electronics enclosure rating to IP 20/NEMA 1.

**Measuring everything that matters:
usa.siemens.com/level**

**Siemens Process Instrumentation offers
best-in-class measurement and seamless
integration into your automation system.
We are the total solution provider for flow,
level, pressure, temperature, weighing,
positioners and more.**

Follow us on:

www.facebook.com/siemensii

<https://twitter.com/siemensii>

www.youtube.com/siemens

<https://blogs.siemens.com/measuringsuccess>



Siemens Industry, Inc.
Process Industries and Drives
100 Technology Drive
Alpharetta, GA 30005
1-800-365-8766
info.us@siemens.com

Subject to change without prior notice

Order No.: PIBR-5MA03-0418

All rights reserved

Printed in USA

© 2018 Siemens Industry, Inc.

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

All product designations may be registered trademarks of Siemens AG. All other designations in this document may represent trademarks whose use by third parties for their own purposes may violate the proprietary rights of the owner.